



Head rotation angles with blade tilted at 90°




Head rotation angles with blade tilted at 45°









FIXED HEAD	MOBILE HEAD	MINIMUM CUT
90°	90°	470 mm








FIXED HEAD	MOBILE HEAD	RECOVERY OF SHORT EXTRUDED PIECES
90° *	90° *	110* mm

^{*}with manual stop kit








FIXED HEAD	MOBILE HEAD	MINIMUM CUT
90°	45°	640 mm








FIXED HEAD	MOBILE HEAD	RECOVERY OF SHORT EXTRUDED PIECES
90° *	45° *	280* mm

^{*}with manual stop kit








FIXED HEAD	MOBILE HEAD	MINIMUM CUT
90°	22,5°	740 mm








FIXED HEAD	MOBILE HEAD	RECOVERY OF SHORT EXTRUDED PIECES
90° *	22,5° *	380* mm

^{*}with manual stop kit








FIXED HEAD	MOBILE HEAD	MINIMUM CUT
45°	45°	800 mm








FIXED HEAD	MOBILE HEAD	MINIMUM CUT
22,5°	22,5°	1020 mm








FIXED HEAD	MOBILE HEAD	MINIMUM CUT
90°	135°	770 mm








FIXED HEAD	MOBILE HEAD	RECOVERY OF SHORT EXTRUDED PIECES
90° *	135° *	410* mm

^{*}with manual stop kit








FIXED HEAD	MOBILE HEAD	MINIMUM CUT
90°	140°	800 mm







FIXED HEAD	MOBILE HEAD	RECOVERY OF SHORT EXTRUDED PIECES
90° *	140° *	440* mm

^{*}with manual stop kit

